




Sumitomo Drive Technologies

A global power transmission solutions provider. With facilities strategically located throughout the world, providing comprehensive products and services in your region.


Headquarter (Manila)



C4 & C5 Bldgs, Granville Industrial Complex, Governor's Drive, Bo. Bancal, Carmona, 4116 Cavite

email: sca.smph-enquiry@shi-g.com

phone: +63 285844921



Extended warranty programs are available on request.

The Most Reliable and Highest Quality Products Backed by a 400 Year Heritage.

Why Choose Sumitomo?

Your drive will be repaired to the original factory like new specifications with warranty using Sumitomo manufactured parts.

Our personnel are the industry's most versed gearbox problem solvers with centuries worth of experience. We provide both standard and tailored services, for maximum gearbox life.

All Gearbox Serviceable

Through our drop-in technology, our team is able to provide solution for obsolete and unsupported models, provide solution for existing model issues such as overheating, oil leaks, ratio change and gear upgrades etc.

Our latest gear technology is integrable for longer lasting performance and future-proof for future retrofits.

Repairs

Scheduled & Emergency Repair

Scheduled and emergency repair services as a one-stop-shop for all your related gearbox needs.

Root Cause Investigation


Aftermarket

We apply a wide range of approaches, tools, and techniques to uncover the causes of your problems.

Inspection Reports

Data

Professional, industry leading inspection reports detail findings, and highlight repairs required to return your gearbox to like-new condition.



Commissioning & Start-up Services

The Key to Long Life

Most of the services offered and customized training can be performed on location.

Field Services


For Your Convenience

Most of the services offered and customized training can be performed on location.


Products Serviced



P4 HANSEN P4



PX PARAMAX® 9000




U UNIMINER



HB CYCLO® HBB



C CYCLO® 6000



H HYPONIC®



B4 CYCLO® BBB4



B5 CYCLO® BBB5



HS HSM