



PREST[®] NEO Compact Gearmotor

Innovative Compact Gearmotor with Unparalleled Benefits



Low Noise


Gears are designed with high contact ratio and high stiffness to lower the noise.

Compact Terminal Box

- Compact Terminal Box (0.1kW~2.2kW).
- For brake, built-in rectifier in the terminal box (40W~90W built in brake parts).

Compact Housing Design

Parallel shaft gear motor in compact new design with high rigidity casing and motor.




High Radial Load Capacity


High Radial Capacity Bearing and High stiffness casings to increase Radial Load Capacity.

Excellent Sealing Performance

Triple-lip seal for leakage protection.



Triple-lip Seal



- ◆ Capacity: 0.1~2.2kW
- ◆ Reduction Ratio: 3~200
- ◆ Motor Options: 3-Phase, IE1, IE2, IE3
Brake
Inverter Duty
CE, JIS, CCC, UL, NEMA, CSA